

Datasheet Expansion alloys

# Osprey® Fe29Ni17Co

Osprey<sup>®</sup> Fe29Ni17Co is an expansion alloy with a coefficient of thermal expansion similar to borosilicate glass.

UNS

K94610

Powder designed for

- Additive Manufacturing (AM)
- Metal Injection Moulding (MIM)



# **Product description**

Osprey<sup>®</sup> Fe29Ni17Co is an expansion alloy with a coefficient of thermal expansion similar to borosilicate glass. Osprey<sup>®</sup> Fe29Ni17Co is an alloy of the same type as Kovar<sup>®</sup>\*.

The powder for Metal Injection Moulding (MIM) has material properties that achieve typical values and exceed minimum values, according to MPIF Standard 35.

This metal powder is manufactured by Inert Gas Atomization (IGA), producing a powder with a spherical morphology which provides good flow characteristics and high packing density. In addition, the powder has a low oxygen content and low impurity levels, resulting in a metallurgically clean product with enhanced mechanical performance.

\*Kovar<sup>®</sup> is a trademark owned by CRS Holding.



## Chemical composition (nominal), %

Last updated: Jul 18, 2023 9:00 AM CET

Fe	Bal.
Cr	0.2
Ni	28.5-29.5
Со	16.5-17.5
С	0.02
Mn	0.5
Si	0.2
AI	0.01

## Powder characteristics and morphology Powder for Additive Manufacturing

Osprey<sup>®</sup> metal powder for Additive Manufacturing is characterized by a spherical morphology and high packing density, which confer good flow properties. For powder bed processes these are essential when applying fresh powder layers to the bed to ensure uniform and consistent part build.

For blown powder processes, such as Direct Energy Deposition (DED), good flow ensures uniform build rates. Tight control of the particle size distribution also helps ensure good flowability. Low oxygen powders result in clean microstructures and low inclusion levels in the finished parts.

#### **Powder for Metal Injection Moulding (MIM)**


Osprey<sup>®</sup> MIM powder has a spherical morphology, resulting in high packing density. This enables the manufacture of feedstocks with high powder loading, which not only minimizes binder costs but also reduces part shrinkage during debinding and sintering. Spherical powder also has excellent flow characteristics, resulting in reduced tool wear and consistent mould filling.

Osprey<sup>®</sup> MIM powder's low oxygen content allows better control of carbon and consistency during sintering. Low oxygen levels, together with high packing density, also facilitate faster sintering.



### Particle size distribution Powder for Additive Manufacturing

Osprey<sup>®</sup> metal powder for Additive Manufacturing is available in a wide range of particle size distributions that are tailored to the individual Additive Manufacturing systems. They can also be tailored to the particular requirements of the end application, both in terms of mechanical performance and surface finish.



Typical particle size distributions for Additive Manufacturing.

Process technology	Size (µm)
Binder jetting	≤ 16, ≤ 22, ≤ 32, ≤ 38, ≤ 45
Laser - Powder Bed Fusion (L-PBF)	15 to 53 and 10 to 45
Electron beam - Powder Bed Fusion (E-PBF)	45 to 106
Direct Energy Deposition (DED)	53 to 150

#### **Powder for Metal Injection Moulding (MIM)**

Osprey<sup>®</sup> metal powder for Metal Injection Moulding (MIM) is available in a wide range of particle size distributions, from under 5  $\mu$ m up to 38  $\mu$ m. The table shows our standard particle size distributions for MIM powders.

Size (µm)	D10 (µm)	D50 (µm)	D90 (µm)
≤ 38	5.5	13.0	31.0
≤ 32	5.0	12.0	29.0



80% ≤ 22	4.5	11.5	27.0
90% ≤ 22	4.0	10.5	22.0
90% ≤ 16	3.5	8.0	16.0

\*Particle size measurements performed using a Malvern laser particle size analyzer, typical D10, D50 and D90 provided.

Tailor-made particle size distributions are available on request. Contact us to discuss your specific requirements.

## Testing

All Osprey<sup>®</sup> metal powders are supplied with a certificate of analysis containing information on the chemical composition and particle size distribution. Information on other powder characteristics is available upon request.

## Packaging

A wide range of packaging options is available, from 5kgs plastic bottles to 250kg metal drums.

5 kg (11 lbs) Plastic bottles 6 kg (13 lbs) Plastic bottles 10 kg (22 lbs) Plastic bottles 20 kg (44 lbs) Metal cans 100 kg (220 lbs) Steel drums 150 kg (330 lbs) Steel drums 250 kg (551 lbs) Steel drums All packaging materials are suitable for air, sea and road freight.

Contact us for more information and to discuss your packaging requirements.

Disclaimer: Data and recommendations are provided for information and guidance only, and the performance or suitability of the material for specific applications are not warranted or guaranteed. Continuous development may necessitate changes in technical data without notice. This datasheet is only valid for Sandvik materials. Datasheet updated: Sep 8, 2023 2:16 PM CET (supersedes all previous editions)